


# Two-hand control block ZSB-1/8

Part number: 3527

FESTO

Safety component with two-hand operation.



## Data sheet

| Feature                                   | Value  |
|---|--|
| Nominal size                              | 4 mm   |
| Type of actuation                         | pneumatic  |
| Design structure                          | Poppet valve with spring return                                |
| Working pressure                          | 3 ... 8 bar  |
| Standard nominal flow rate                | 50 l/min   |
| Operating medium                          | Compressed air in accordance with ISO8573-1:2010 [7:4:4]       |
| CE symbol (see declaration of conformity) | according to EU machines guideline                             |
| Ambient temperature                       | -10 ... 60 °C  |
| Product weight                            | 490 g  |
| Mounting type                             | with through hole<br>with internal (female) thread<br>Optional |
| Auxiliary pilot air port 12               | G1/8   |
| Auxiliary pilot air port 14               | G1/8   |
| Pneumatic connection, port 1              | G1/8   |
| Pneumatic connection, port 2              | G1/8   |
| Pneumatic connection, port 3              | G1/8   |
| Pneumatic connection, port 4              | G1/8   |
| Pneumatic connection, port 5              | G1/8   |
| Materials information for cover           | Aluminum die cast  |
| Materials information for seals           | NBR  |
| Materials information, housing            | Wrought Aluminum alloy<br>Anodized                             |