

Economy air gun LSP-1/4-D

Part number: 35528

FESTO

Die-cast metal design.



Data sheet

Feature	Value
Exhaust-air function	Air jet can be dosed
Working pressure	0 ... 10 bar
Flow rate to atmosphere	120 l/min
Standard nominal flow rate	120 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364 zone III
Sound pressure level	90 dB(A)
Ambient temperature	-10 ... 50 °C
Product weight	240 g
Pneumatic connection	Female thread 1/4
Materials note	Conforms to RoHS
Material housing	Wrought Aluminum alloy