

Female hose connector

N-1/4-P-9

Part number: 3607

FESTO

With sealing ring.



Data sheet

| Feature | Value |
|---|---|
| Nominal size | 6.5 mm |
| Type of seal on screw-in stud | Sealing ring |
| Assembly position | Any |
| Design | Straight design |
| Container size | 1 |
| Operating pressure complete temperature range | -0.95 ... 16 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:::] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 ... 60 °C |
| Max. tightening torque | 12 Nm |
| Product weight | 7.14 g |
| Pneumatic connection, port 1 | Male thread G1/4 |
| Pneumatic connection, port 2 | For tubing internal diameter 9 mm |
| Materials note | Conforms to RoHS |
| Material housing | Anodised aluminium |