

# Suction cup VAS-30-1/8-PUR

Part number: 36137

FESTO

With sealing ring OL.



## Data sheet

Feature	Value
Nominal size	3 mm
suction cup diameter	30 mm
Effective suction diameter	25 mm
Design structure	Vacuum connection at top round, standard
Operating medium	Atmospheric air
Ambient temperature	-20 ... 60 °C
Breakaway force at 70% vacuum	34 N
Mounting thread	G1/8
suction cup mounting	G 1/8
Vacuum connection	G1/8
Shore hardness	62
Materials information for screw-in stud	Zinc die-casting
Materials information for suction cup	TPE-U(PU)