

Axial kit


EAMM-A-S38-57A-G2

Part number: 3637956

★ Core product range

Suitable for electric drives.

FESTO



Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	6.5 Nm
Product weight	340 g
Interface code, actuator	S38
Interface code, motor in	57A
Materials note	Conforms to RoHS