

# Plastic tubing

## PP-4-NT

Part number: 4231

FESTO

For CK and CN connectors, suitable for higher pressures and temperatures, polyamide (not approved for use in the food industry).  
Type to be discontinued. Available until 2011.



### Data sheet

Feature	Value
Outside diameter	6 mm
Bending radius relevant for flow rate	32 mm
Inside diameter	4 mm
Min. bending radius	14 mm
Temperature dependent working pressure	-0.95 ... 19 bar
Operating medium	Filtered compressed air Vacuum
Ambient temperature	-30 ... 80 °C
Authorization	Germanischer Lloyd TÜV
Product weight according to length	0.0163 kg/m
Color	neutral
Shore hardness	D 55 +/-3
Materials note	Free of copper and PTFE
Materials information for tubing	TPE-A