

# Plastic tubing PP-3-NT

Part number: 4572

FESTO

For CK and CN connectors, suitable for higher pressures and temperatures, polyamide (not approved for use in the food industry).  
Type to be discontinued. Available until 2011.



## Data sheet

| Feature                                | Value                             |
|--|-----------------------------------|
| Outside diameter                       | 4 mm                              |
| Bending radius relevant for flow rate  | 18 mm                             |
| Inside diameter                        | 2.9 mm                            |
| Min. bending radius                    | 12 mm                             |
| Temperature dependent working pressure | -0.95 ... 15 bar                  |
| Operating medium                       | Filtered compressed air<br>Vacuum |
| Ambient temperature                    | -30 ... 80 °C                     |
| Authorization                          | Germanischer Lloyd<br>TÜV         |
| Product weight according to length     | 0.0062 kg/m                       |
| Color                                  | neutral                           |
| Shore hardness                         | D 55 +/-3                         |
| Materials note                         | Free of copper and PTFE           |
| Materials information for tubing       | TPE-A                             |