

# Plastic tubing PUN-V0-12x2-GE

Part number: 525461

FESTO

Flame retardant



## Data sheet

Feature	Value
Outside diameter	12 mm
Bending radius relevant for flow rate	62 mm
Inside diameter	8 mm
Min. bending radius	21 mm
Temperature dependent working pressure	-0.95 ... 10 bar
Operating medium	Filtered compressed air Vacuum
Fire class in accordance with UL 94	V0-V2
Ambient temperature	-35 ... 60 °C
Authorization	TÜV
Product weight according to length	0.08 kg/m
Color	yellow
Note on colour	Due to flame protection deviation from the standard colour
Shore hardness	D 54 +/-3
Materials note	Free of copper and PTFE
Materials information for tubing	TPE-U(PU)