

Plug SEA-GS-HAR-4POL

Part number: 525928
Product to be discontinued

FESTO

[For valve manifolds.](#)

[Type to be discontinued. Available until 2023. See Support Portal for alternative products.](#)



Data sheet

| Feature | Value |
|---|--|
| Based on the standard | EN 61076-2-101 EN 61984 |
| Mounting type | with thread |
| Assembly position | Any |
| Product weight | 11.5 g |
| Electrical connection | 4-pin M12x1 Straight plug / insulation displacement connection |
| Operating voltage range DC | ≤ 32 V |
| Operating voltage range AC | ≤ 32 V |
| Acceptable current load at 40°C | 4 A |
| Surge strength | 0.8 kV |
| Cable gland connection | Pg9 |
| Permissible cable diameter | 4 ... 5.1 mm |
| Permissible individual wire diameter | 0.1 mm |
| Permissible wire diameter | 1.2 ... 1.6 mm |
| Terminal cross-section | 0.25 ... 0.5 mm ² |
| Protection class | IP67 |
| Ambient temperature | -25 ... 85 °C |
| Materials note | Conforms to RoHS |
| Degree of contamination | 3 |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| Material housing | Zinc die-casting Nickel plated |
| Permissible wire insulation | PVC |