


Vacuum generator

VN-30-L-T6-PI5-VI6-RO2

Part number: 526132

FESTO

Standard, high suction rate, width 24 mm, T shape with internal thread and open silencer.



Data sheet

Feature	Value
Nominal size, Laval nozzle	3 mm
Grid dimension	24 mm
Design, silencer	open
Assembly position	Any
Ejector characteristic	High suction flow rate Standard
Integrated function	Open silencer
Design structure	T-shaped
Working pressure for max. suction rate	6 bar
Working pressure	1 ... 8 bar
Nominal working pressure	6 bar
Max. suction rate with respect to atmosphere	339 l/min
Air supply time at nominal working pressure	0.1 s
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364 zone III
Medium temperature	0 ... 60 °C
Noise level at nominal operating pressure	70 dB(A)
Ambient temperature	0 ... 60 °C
Max. tightening torque	0.8 Nm
Product weight	183 g
Mounting type	with through hole with accessories
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 3	Open silencer
Vacuum connection	G3/8
Material of connecting thread	Wrought aluminum alloy, anodized
Materials note	Conforms to RoHS
Material seals	NBR
Material receiver nozzle	POM
Material housing	POM-reinforced
Material silencer	Aluminum die cast POM PU foam
Material transmitter nozzle	Wrought Aluminum alloy