


# Round cylinder DSNU-40-15-P-A

Part number: 5262530

FESTO



## Data sheet

| Feature                                  | Value  |
|--|--|
| Stroke                                   | 15 mm  |
| Piston diameter                          | 40 mm  |
| Piston rod thread                        | M12x1.25   |
| Cushioning                               | Elastic cushioning rings/pads at both ends                         |
| Mounting position                        | Any  |
| Structural design                        | Piston<br>Piston rod<br>Cylinder barrel                            |
| Position sensing                         | For proximity sensor   |
| Operating pressure                       | 0.1 MPa...1 MPa<br>1 bar...10 bar                                  |
| Mode of operation                        | Double-acting  |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 2 - Moderate corrosion stress                                      |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L  |
| Ambient temperature                      | -20 °C...80 °C   |
| Theoretical force at 6 bar, retracting   | 633.3 N  |
| Theoretical force at 6 bar, advancing    | 752.9 N  |
| Moving mass                              | 254 g  |
| Product weight                           | 697 g  |
| Type of mounting                         | With accessories   |
| Pneumatic connection                     | G1/4   |
| Note on materials                        | RoHS-compliant   |
| Cover material                           | Wrought aluminum alloy   |
| Seals material                           | NBR<br>TPE-U(PU)   |
| Piston rod material                      | High-alloy steel   |
| Material of cylinder barrel              | High-alloy stainless steel   |