

Pressure gauge



MA-27-10-M5

Part number: 526323
Product to be discontinued

FESTO

With display unit in bar.

Type to be discontinued. Available until 2023. See Support Portal for alternative products.



Data sheet

Feature	Value
Indicating range [bar]	0 ... 10 bar
Nominal size of pressure gauge	27
Design structure	Bourdon-tube pressure gauge
Mounting type	Line installation
Operating medium	Inert gases Neutral fluids
Working pressure	0 ... 10 bar
Alternating load factor	0.66
Measurement accuracy class	4
Protection class	IP43
Medium temperature	0 ... 60 °C
Ambient temperature	0 ... 60 °C
Materials note	Conforms to RoHS
Position of connection	Rear side central
Pneumatic connection	M5
Materials in contact with media	Brass
Material of threaded plug	Brass
Material housing	PA
Material screen	PS
Housing color	Black
Product weight	11 g
Note on operating and pilot medium	No acetylene No oxygen