

Connecting cable KMP6-26P-16-2,5



Part number: 527546

Classic - do not use for new projects

FESTO

For valve manifold CPV-SC, with 26-pin Sub-D plug, 2.5 m long.

Modern alternatives can be found by entering the first four characters of the type code in the search field.



Data sheet

Feature	Value
Conforms to standard	DIN 41652
Cable identification	Without inscription label holder
Connection frequency	50
Product weight	280 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	Angular
Electrical connection 1, connection type	Plug socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	26
Electrical connection 1, occupied pins/wires	20
Electrical connection 1, type of mounting	2 screws 4-40 UNC
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	20
Electrical connection 2, occupied pins/wires	20
Operating voltage range DC	0 ... 30 V
Nominal operating voltage DC	24 V
Acceptable current load at 40°C	2.8 A
Surge strength	1 kV
Cable length	2.5 m
Cable attribute	Standard
Test conditions of cable	Test conditions on request
Bending radius, fixed cable installation	≥ 88 mm
Bending radius, flexible cable installation	≥ 132 mm
Cable diameter	8.8 mm
Cable diameter tolerance	± 0,25 mm
Cable structure	20x0,25
Nominal conductor cross-section	0.25 mm ²
Wire ends	Cut off bluntly
Protection class	IP40
Note on degree of protection	in assembled condition
Ambient temperature	-25 ... 70 °C
Ambient temperature with flexible cable installation	-5 ... 70 °C
Storage temperature	-25 ... 75 °C
CE symbol (see declaration of conformity)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materials note	Conforms to RoHS
Degree of contamination	2
Material cable sheath	PVC

Feature	Value
Cable sheath color	Grey
Material housing	PBT-reinforced
Housing color	Grey
Material screw-type lock	Nickel-plated brass
Material electrical contact	Gold-plated copper alloy