

Service unit FRC-1/8-D-7-O-5M-MICRO-H

Part number: 527867



Classic - do not use for new projects

With threaded connection plate, without pressure gauge,
semiautomatic condensate drain

Modern alternatives can be found by entering the first four characters
of the type code in the search field.

Type to be discontinued. Available until 2023. See Support Portal for
alternative products.

FESTO



Data sheet

Feature	Value
Size	Micro
Series	D
Actuator lock	Rotary knob with lock
Assembly position	Vertical +/- 5°
Condensate drain	semi-automatic
Design structure	Filter regulator without pressure gauge proportional standard mist lubricator
Max. condensate volume	3 cm ³
Grade of filtration	5 µm
Pressure gauge	M5 ready
Working pressure	1 ... 10 bar
Pressure regulation range	0.5 ... 7 bar
Max. pressure hysteresis	0.3 bar
Standard nominal flow rate	160 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [-:--]
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Product weight	139 g
Mounting type	Line installation with accessories
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	G1/8
Material housing	Wrought Aluminum alloy
Material bowl	PC