

# Service unit FRC-N1/8-D7-O-5M-MICRO-H



Part number: 527871  
Product to be discontinued

FESTO

With threaded connection plate, without pressure gauge, semiautomatic condensate drain

This product is only available if ordered from the Festo Corporation, USA.

Type to be discontinued. Available until 2016. See Support Portal for alternative products.



## Data sheet

Feature	Value
Size	Micro
Assembly position	Vertical
Grade of filtration	5 µm
Condensate drain	semi-automatic
Working pressure	1 ... 10 bar
Pressure regulation range	0.5 ... 7 bar
Standard nominal flow rate	140 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [-::-]
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Product weight	123 g
Mounting type	Line installation With mounting bracket Optional
Pneumatic connection, port 1	NPT1/8-27
Pneumatic connection, port 2	NPT1/8-27
Materials information, housing	Wrought Aluminum alloy
Materials information for bowl	PC