


Driver FKC-8/12

Part number: 529350

FESTO

for linear drive DGC-G.



Data sheet

Feature	Value
Size	8/12
Radial deviation +/-	2.5 mm
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 60 °C
Brief maximum permitted load in force direction +/-	1,100 N
Long maximum permitted load in force direction +/-	550 N
Product weight	29.3 g
Materials note	Conforms to RoHS
Material joint	PA-reinforced
Material on ball stud	High alloy steel
Material plate	Wrought Aluminum alloy