



# Branching module MS6-FRM-1/2-Y-Z

Part number: 529855

FESTO

Includes pressure switch without indicator, direction of flow: from right to left.



## Data sheet

Feature	Value
Assembly position	Any
Design structure	Branching module
Working pressure	0 ... 12 bar
Standard nominal flow rate in main flow direction 1→2	14,700 l/min
Standard nominal flow rate outlet at top	4,400 l/min
Standard nominal flow rate outlet at bottom	4,600 l/min
Operating voltage range AC	0 ... 250 V
Operating voltage range DC	0 ... 125 V
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-10 ... 60 °C
Food-safe	See Supplementary material information
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Product weight	736 g
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Pneumatic connection, port 3	G1/2
Pneumatic connection, port 4	G1/2
Materials note	Conforms to RoHS
Material housing	Aluminum die cast