

Coupling EAMC-40-66-12-19

Part number: 529952

FESTO

For electromechanical drive with servomotor



Data sheet

Feature	Value
Holder diameter 1	12 mm
Holder diameter 2	19 mm
Size	40
Nominal length	66 mm
Assembly position	Any
Max. speed	6,500 1/min
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 ... 60 °C
Mass moment of inertia	42.3 kgmm ²
Transferable torque	21 Nm
Product weight	139 g
Materials note	Conforms to RoHS