


Coupling plug KS2-CN-4

Part number: 531663
Product to be discontinued

FESTO

For self-closing quick coupling connectors.

Type to be discontinued. Available until 2019. See Support Portal for alternative products.



Data sheet

Feature	Value
Nominal size	2.4 mm
Operating pressure complete temperature range	-0.95 ... 12 bar
Standard nominal flow rate	119 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	-10 ... 80 °C
Product weight	5 g
Pneumatic connection, port 1	CN-4
Materials note	Conforms to RoHS