

# Lubricator MS6N-LOE-3/8-U-Z

Part number: 531721

FESTO

Metal bowl, direction of flow: from right to left.



## Data sheet

Feature	Value
Size	6
Series	MS
Assembly position	Vertical +/- 5°
Design structure	proportional standard mist lubricator
Max. oil capacity	80 cm <sup>3</sup>
Bowl guard	Metal bowl guard
Inlet pressure 1	1 ... 16 bar
Minimum flow rate for lubricator function	50 l/min
Standard nominal flow rate	5,300 l/min
Operating medium	Filtered compressed air, 40 µm filtration
Corrosion resistance classification CRC	2
Storage temperature	-10 ... 60 °C
Medium temperature	0 ... 60 °C
Oil viscosity	ISO VG 32
Ambient temperature	0 ... 60 °C
Product weight	810 g
Mounting type	with accessories Optional Line installation
Pneumatic connection, port 1	NPT3/8-18
Pneumatic connection, port 2	NPT3/8-18
Materials information, housing	Aluminum die cast
Materials information for bowl	Wrought Aluminum alloy