

Union nut MCK-PK-4-KD

Part number: 533673

FESTO

Metal version.



Data sheet

Feature	Value
Size	Female thread M10x1
Operating pressure for entire temperature range	-0.095 ... 1.2 MPa
Operating pressure complete temperature range	-0.95 ... 12 bar
Operating pressure for entire temperature range	-13.775 ... 174 psi
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-10 ... 60 °C
Pneumatic connection, port 1	For tubing outside diameter 6 mm for barbed connector internal diameter 4 mm with nut
Material of union nut	Wrought aluminium alloy, nickel-plated
Materials note	Conforms to RoHS