

Filter regulator MS12-LFR

Part number: 535022

FESTO

For manifold assembly, with G thread.



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Size	12
Series	MS
Actuator lock	Rotary knob with lock Rotary knob with integrated lock with accessories, lockable
Assembly position	Vertical +/- 5°
Design structure	Filter regulator with pressure gauge
Pressure gauge	with pressure gauge
Max. pressure hysteresis	0.4 bar
Operating medium	Compressed air to ISO 8573-1:2010 [-:4:-] Compressed air in accordance with ISO8573-1:2010 [7:4:-] Inert gases
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-10 ... 60 °C
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Mounting type	Line installation with accessories Optional
Material housing	Aluminum die cast
Material bowl	Wrought Aluminum alloy