


# Pressure build-up valve MS12-DL

Part number: 535033

FESTO

For manifold assembly, with G thread.



## Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Exhaust-air function	throttleable
Type of actuation	pneumatic
Assembly position	Any
Manual override	None
Design structure	Piston seat
Type of reset	mechanical spring
Type of piloting	direct
Pilot air supply	Internal
Flow direction	non reversible
Valve function	2/2
Working pressure	2 ... 20 bar
Standard nominal flow rate	25,000 ... 42,000 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Product weight	3,600 g
Mounting type	Line installation with accessories Optional
Material seals	NBR
Material housing	Aluminum die cast