

Fine filter MS12N-LFM

Part number: 535045

FESTO

With NPT thread



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Series	MS
Size	12
Design structure	Fiber filter
Working pressure	0.8 ... 20 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [6:8:4] Inert gases
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Storage temperature	-10 ... 60 °C
Mounting type	Line installation with accessories Optional
Assembly position	Vertical +/- 5°
Material housing	Aluminum die cast
Material filter	Boron silicate fiber
Material bowl	Wrought Aluminum alloy
Materials note	Conforms to RoHS