

Filter MS4-LF-1/4-EUV-Z

Part number: 535659

FESTO

40 µm filter, metal bowl guard, fully automatic condensate drain, flow direction from right to left.



Data sheet

| Feature | Value |
|---|---|
| Size | 4 |
| Series | MS |
| Assembly position | Vertical +/- 5° |
| Grade of filtration | 40 µm |
| Condensate drain | fully automatic |
| Design structure | Sintered filter with centrifugal separator |
| Max. condensate volume | 25 ml |
| Bowl guard | integrated as metal shell |
| Inlet pressure 1 | 2 ... 12 bar |
| Standard nominal flow rate | 1,700 l/min |
| Operating medium | Compressed air |
| Corrosion resistance classification CRC | 2 |
| Storage temperature | -10 ... 60 °C |
| Air purity class at output | 5:7:- per DIN ISO 8573-1 |
| Medium temperature | 5 ... 60 °C |
| Ambient temperature | 5 ... 60 °C |
| Product weight | 349 g |
| Mounting type | with accessories Optional Line installation |
| Pneumatic connection, port 1 | G1/4 |
| Pneumatic connection, port 2 | G1/4 |
| Materials note | Free of copper and PTFE |
| Materials information for seals | NBR |
| Materials information for filter | PE |
| Materials information, housing | Aluminum die cast |
| Materials information for bowl | Aluminum die cast Wrought Aluminum alloy |
| Materials info, viewing window | PA |