

Plastic tubing PLN-16X2-SW

Part number: 539065

FESTO

highly resistant to chemicals and hydrolysis.



Data sheet

Feature	Value
Outside diameter	16 mm
Bending radius relevant for flow rate	95 mm
Inside diameter	12 mm
Min. bending radius	55 mm
Temperature-dependent operating pressure	-0.095 ... 1.4 MPa
Temperature dependent working pressure	-0.95 ... 14 bar
Temperature-dependent operating pressure	-13.775 ... 203 psi
Note on working pressure	Water: max. 0.6 MPa at 0 - 50 °C
Authorization	TÜV
Certificate issuing department	B 013277 0506 00
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-] Water (liquid, free of ice)
PWIS conformity	VDMA24364-B2-L
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See Supplementary material information
Ambient temperature	-30 ... 80 °C
Product weight according to length	0.082 kg/m
Pneumatic connection	For push-in connector outside diameter 16 mm
Color	Black
Materials note	Conforms to RoHS
Material tubing	PE