


# Connecting cable NEBU-M5G4-K-1-Q3-M8G3

Part number: 539510

FESTO

for proximity sensors, position transmitter, pressure switch, flow sensors, visual and inductive sensors.



## Data sheet

Feature	Value
Cable attribute	Suitable for chain link trunking
Operating voltage range AC	30 V
Operating voltage range DC	30 V
Permissible current load	1.7 A
Degree of contamination	3
Protection class	IP65 IP67
Max. tightening torque, plug socket	0.3 Nm
Max. tightening torque plug	0.3 Nm
Min. cable bending radius	30 mm
Electrical connection	4-pin / 3-pin M5x0,5 / M8x1 Plug straight / socket straight
Cable structure	3 x 0,14 mm <sup>2</sup>
Cable diameter	2.9 mm
Cable length	1 m
Cable type	LiFY11Y
Nominal conductor cross-section	0.14 mm <sup>2</sup>
Mounting type	With knurled nut With sleeve nut
Housing color	Black
Cable sheath color	Grey
Materials information for locknut	Brass Nickel plated
Materials information, housing	TPE-U(PU)
Materials information, cable sheaths	TPE-U(PU)
Material information for crimp connectors	Brass Gold plated