


Pick&Place DHSP-SLT16-SLT10

Part number: 542968

FESTO

comprising mini slides, precise, compact, short cycle times. Defined interfaces to Festo's rotary and gripper range. Order as a mounting kit or completely assembled and installed.

Please click above on symbol FAX request, to obtain a non-binding offer to fulfill your requirements.



Data sheet

Feature	Value
Assembly	Pick&Place 1.0
Effective load	0 ... 2 kg
Drive unit, Z axis	SLT-10
Drive system, Z axis	Pneumatic
Stroke, Z axis	0 ... 80 mm
Repetition accuracy in the end position, Z axis	± 0,02 mm
Repetition accuracy in the intermediate position, Z axis	± 0,02 mm
Drive unit, Y axis	SLT-16
Drive system, Y axis	Pneumatic
Stroke, Y axis	0 ... 150 mm
Repetition accuracy in the end position, Y axis	± 0,02 mm
Repetition accuracy in the intermediate position, Y axis	± 0,02 mm