


Driver FKC-50/63

Part number: 545240

FESTO

for linear drive DGC-G.



Data sheet

Feature	Value
Size	50/63
Radial deviation +/-	4 mm
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 60 °C
Brief maximum permitted load in force direction +/-	5,000 N
Long maximum permitted load in force direction +/-	5,000 N
Product weight	1,200 g
Materials note	Conforms to RoHS
Material mounting pin	High alloy steel
Material joint	High alloy steel
Material thread piece	Steel
Material plate	Aluminum casting
Material lock	Spring steel