

Plastic tubing PUN-5/32X1/32-U-SW

Part number: 546579

FESTO

standard O.D. tubing, suitable for QS and QB push-in fittings.

This product is only available if ordered from the Festo Corporation, USA.

Old part no. 13013792



Data sheet

| Feature | Value |
|--|-----------------------------------|
| Outer diameter, inches | 5/32 |
| Inner diameter, inches | 3/32 |
| Min. bending radius | 0.202 " |
| Temperature dependent working pressure | -14 ... 150 Psi |
| Operating medium | Filtered compressed air Vacuum |
| Ambient temperature | -68 ... 140 °F |
| Product weight according to length | 0.103 oz/ft |
| Color | Black |
| Shore hardness | A 98 +/-3 |
| Materials note | Free of copper and PTFE |
| Materials information for tubing | TPE-U(PU) |