

# Plastic tubing

## PUN-1/4X3/64-U-RT-300

Part number: 546641

FESTO

standard O.D. tubing, suitable for QS and QB push-in fittings.

This product is only available if ordered from the Festo Corporation, USA.

Old part no. 13028505



### Data sheet

Feature	Value
Outer diameter, inches	1/4
Inner diameter, inches	5/32
Min. bending radius	0.476 "
Temperature dependent working pressure	-14 ... 150 Psi
Operating medium	Filtered compressed air Vacuum
Ambient temperature	-68 ... 140 °F
Product weight according to length	0.251 oz/ft
Color	Red
Shore hardness	A 98 +/-3
Materials note	Free of copper and PTFE
Materials information for tubing	TPE-U(PU)