

# Adapter NEFC-M12G5-0.3-U1G5

Part number: 547432

FESTO



## Data sheet

Feature	Value
Mounting type	Threaded
Electrical connection	5-pin M12x1 Plug
Cable length	0.3 m
Cable structure	4x0,34
Protection class	IP20
Ambient temperature	-5 ... 50 °C
CE symbol (see declaration of conformity)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materials note	Conforms to RoHS
Corrosion resistance classification CRC	0 - No corrosion stress
Material cable sheath	PUR
Material housing	ABS
Material electrical contact	Brass, gold-plated