

Shock absorber DYSW-5-8-Y1F

Part number: 548071

FESTO

Self-adjusting, with progressive characteristic curve.



Data sheet

Feature	Value
Size	5
Stroke	8 mm
Cushioning	self-adjusting Soft characteristic
Assembly position	Any
Position detection	No
Max. impact speed	2 m/s
Reset time short	0.2 s
Reset time long	1 s
Mode of operation	single-acting pushing action
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-10 ... 80 °C
Cushioning length	8 mm
Max. stop force	200 N
Max. energy consumption per stroke	1.3 J
Max. energy consumption per hour	10,000 J
Max. residual energy	0.01 J
Reset force	0.9 N
Product weight	11 g
Mounting type	with lock nut
Materials note	Conforms to RoHS
Material seals	NBR
Material housing	High alloy steel
Material piston rod	High alloy steel