


Stepper motor EMMS-ST-87-S-SB

Part number: 549418

FESTO

Without gear unit/with brake.



Data sheet

Feature	Value
Stepper angle at full step	1.8 deg
Stepper angle tolerance	±5%
Operating voltage DC for brake	24 V
Insulation protection class	B
Power consumption, brake	11 W
Nominal voltage DC	48 V
Nominal motor current	9.5 A
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Storage temperature	-20 ... 70 °C
Relative air humidity	45 - 80 %
Protection class	IP54
Ambient temperature	-10 ... 50 °C
Authorization	C-Tick
Overall mass moment of inertia at power take-off	1.07 kgcm ²
Brake holding torque	2 Nm
Motor holding torque	2.5 Nm
Mass moment of inertia of brake	0.07 kgcm ²
Mass moment of inertia of rotor	1 kgcm ²
Permissible axial shaft load	65 N
Permissible radial shaft load	200 N
Product weight	2,350 g
Electrical connector system	Plug