

# Vacuum filter

## VAF-DB-1/2

Part number: 553141

FESTO

for filtering dirt particles



## Data sheet

| Feature                   | Value  |
|---------------------------|--|
| Assembly position         | Vertical   |
| Grade of filtration       | 80 µm  |
| Working pressure          | -0.95 ... 0 bar  |
| Note on working pressure  | Only for application in open vacuum systems              |
| Operating medium          | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| PWIS conformity           | VDMA24364 zone III                                       |
| Ambient temperature       | -5 ... 50 °C   |
| Max. tightening torque    | 20.5 Nm  |
| Product weight            | 162 g  |
| Mounting type             | Line installation<br>with wall/surface fixing            |
| Pneumatic connection      | G1/2   |
| Vacuum connection         | G1/2   |
| Materials note            | Conforms to RoHS   |
| Material seals            | NBR  |
| Material filter           | PE   |
| Material housing          | PP reinforced  |
| Material bowl             | PA   |
| Ejector pulse suitability | ≤ 7 bar  |