


Bellows kit DADB-V6-80-S376-425

Part number: 553365

FESTO

For standard cylinders to ISO 15552



Data sheet

| Feature | Value |
|---|--|
| Outside diameter | 93 mm |
| Size | 80 |
| Stroke range | 376 ... 425 mm |
| Piston rod extension | 98 mm |
| Design | Round |
| Assembly position | Any |
| Design structure | Bellows kit with ducted exhaust air |
| Corrosion resistance classification CRC | 3 - High corrosion stress |
| PWIS conformity | VDMA24364-B2-L |
| Resistance to media | Dust Chippings Oils Grease Gasolines |
| Protection class | IP54 |
| Ambient temperature | -10 ... 80 °C |
| Product weight | 296 g |
| Mounting type | slip-on With threaded pin |
| Pneumatic connection | G1/4 |
| Materials note | Conforms to RoHS |
| Material adapter components | PA-reinforced |
| Material seals | NBR |
| Material bellows | NBR |
| Material threaded pin | High alloy steel, non-corrosive |