


# Bus interface CECX-F-CO

Part number: 553854

FESTO

For the CECX.



## Data sheet

Feature	Value
Corrosion resistance classification CRC	0 - No corrosion stress
Authorization	c UL us - Listed (OL)
Materials note	Contains PWIS substances Conforms to RoHS
Ambient temperature	5 ... 55 °C
Storage temperature	-40 ... 70 °C
Relative air humidity	10 - 95 %
Safety class	III
Product weight	27 g
Test for insensitivity to vibration	EN 60068-2-6 FC 5 - 9 Hz 3,5 mm 9 - 150 Hz 1g
Test for insensitivity to shock	EN 60068-2-27 EA 15 g, 11 ms (half sine)
Status displays	LED yellow = transmit LED green = receive
Fieldbus interface	CAN-Bus
Fieldbus interface, connection technology	Plug Sub-D 9-pin
Fieldbus interface, transmission rate	125, 250, 500, 800, 1000kbit/s Adjustable via software
Fieldbus interface, electrical isolation	No
CE symbol (see declaration of conformity)	according to EU-EMV guideline