


Bus interface CECX-B-CO

Part number: 553980

FESTO



Data sheet

Feature	Value
Corrosion resistance classification CRC	0 - No corrosion stress
Authorization	c UL us - Listed (OL)
Materials note	Contains PWIS substances Conforms to RoHS
Operating voltage	19,2 - 30 VDC
Output voltage/power	Max. power output 24 V: 45 W Max. power output 5 V: 8.5 W
Power consumption 24 V	6.5 W
Ambient temperature	5 ... 55 °C
Storage temperature	-40 ... 70 °C
Relative air humidity	10 - 95 %
Protection class	IP20
Safety class	III
Product weight	121 g
Test for insensitivity to vibration	EN 60068-2-6 FC 5 - 9 Hz 3,5 mm 9 - 150 Hz 1g
Test for insensitivity to shock	EN 60068-2-27 EA 15 g, 11 ms (half sine)
Electrical connector technology, I/O	Socket strip, grid 5.08 mm
Status displays	LED (status) LED yellow = transmit LED green = receive
Fieldbus interface	CAN-Bus
Fieldbus interface, connection technology	Plug Sub-D 9-pin
Fieldbus interface, transmission rate	125, 250, 500, 800, 1000kbit/s Adjustable via rotary switch
Fieldbus interface, electrical isolation	No