


Bus interface CECX-F-PB-V1

Part number: 553981

FESTO



Data sheet

Feature	Value
Corrosion resistance classification CRC	0 - No corrosion stress
Authorization	c UL us - Listed (OL)
Materials note	Contains PWIS substances Conforms to RoHS
Power consumption 24 V	2 W
Ambient temperature	5 ... 55 °C
Storage temperature	-40 ... 70 °C
Relative air humidity	10 - 95 %
Protection class	IP20
Safety class	III
Product weight	138 g
Test for insensitivity to vibration	EN 60068-2-6 FC 5 - 9 Hz 3,5 mm 9 - 150 Hz 1g
Test for insensitivity to shock	EN 60068-2-27 EA 15 g, 11 ms (half sine)
Status displays	LED yellow = RDY LED yellow = STA LED green = RUN LED red = ERR
Fieldbus interface	PROFIBUS master DP-V1
Fieldbus interface, connection technology	Socket Sub-D 9-pin
Fieldbus interface, transmission rate	9.6 kbit/s up to 12 mbit/s Adjustable via software
Fieldbus interface, electrical isolation	Yes