


Axial kit EAMM-A-A22-55A

Part number: 558896

FESTO

Suitable for cantilever axis EGSA.



Data sheet

| Feature | Value |
|------------------------|------------------------|
| Size | 22 |
| Assembly position | Any |
| Max. speed | 10,000 1/min |
| Storage temperature | -25 ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Protection class | IP40 |
| Ambient temperature | 0 ... 50 °C |
| Mass moment of inertia | 6.06 kgmm ² |
| Transferable torque | 5.1 Nm |
| Product weight | 430 g |
| Materials note | Conforms to RoHS |