


# Axial kit

## EAMM-A-A22-57A

Part number: 558897

FESTO



### Data sheet

Feature	Value
Size	22
Assembly position	Any
Max. speed	8,000 1/min
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	0 ... 50 °C
Mass moment of inertia	6.06 kgmm <sup>2</sup>
Transferable torque	7.5 Nm
Product weight	430 g
Materials note	Conforms to RoHS