


Key switch Q-3-M5

Part number: 561617
Product to be discontinued

FESTO

This type is suitable for vacuum.

Type to be discontinued. Available until 2018. See Support Portal for alternative products.



Data sheet

| Feature | Value |
|---|---|
| Valve function | 3/2 closed, monostable |
| Type of actuation | manual |
| Width | 22.5 mm |
| Standard nominal flow rate | 80 l/min |
| Working pressure | -0.95 ... 8 bar |
| Design structure | Piston seat |
| Type of reset | mechanical spring |
| Nominal size | 2 mm |
| Assembly position | Any |
| Type of piloting | direct |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| Medium temperature | -10 ... 60 °C |
| Ambient temperature | -10 ... 60 °C |
| Actuating force | 23 N |
| Product weight | 480 g |
| Mounting type | with through hole |
| Pneumatic connection, port 1 | M5 |
| Pneumatic connection, port 2 | M5 |
| Materials information for seals | NBR |
| Materials information, housing | Wrought Aluminum alloy Anodized |