

Solenoid coil

VACC-S18-35-A1-1A

Part number: 562907

FESTO

for armature system F10, connection pattern type A, according to EN 175 301, 24 V AC/50-60 Hz.



Data sheet

| Feature | Value |
|---|--|
| Type of actuation | electrical |
| Assembly position | Any |
| Switching position indicator | No |
| Duty cycle | 100 % |
| Insulation class | H |
| Characteristic coil data | 24 V AC: 50/60 Hz, power 3.5 VA |
| Permissible voltage fluctuation | -15 % / +10 % |
| Corrosion resistance classification CRC | 4 - Very high corrosion stress |
| PWIS conformity | VDMA24364 zone III |
| Protection class | IP65 |
| Ambient temperature | -20 ... 60 °C |
| Product weight | 530 g |
| Electrical connection | Plug pattern type A to EN 175301-803 Plug to EN 175301-803 |
| Materials note | Conforms to RoHS |
| Material solenoid coil | PA Steel |