


Branching module MS9-FRM-G-VS-Y

Part number: 564147

FESTO

Includes pressure switch without indicator, direction of flow: from left to right.



Data sheet

Feature	Value
Size	9
Series	MS
Assembly position	Any
Design structure	Branching module
Working pressure	0 ... 12 bar
Operating voltage range AC	0 ... 250 V
Operating voltage range DC	0 ... 125 V
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-10 ... 60 °C
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Product weight	1,100 g
Mounting type	Front panel installation Line installation with accessories Optional
Pneumatic connection, port 3	G1
Pneumatic connection, port 4	G1
Material of cover	PA-reinforced
Materials note	Conforms to RoHS
Material of connecting plate	Aluminum die cast
Material mounting bracket	Aluminum die cast
Material housing	Aluminum die cast
Material module connector	Aluminum die cast