


Blanking plate VABB-L1-10-W

Part number: 566495
★ Core product range

FESTO



Data sheet

Feature	Value
Grid dimension	10.5 mm
Operating pressure MPa	-0.09 ... 1 MPa
Working pressure	-0.9 ... 10 bar
Authorization	RCM Mark c UL us - Recognized (OL)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Product weight	24 g
Materials note	Conforms to RoHS
Material cover plate	PA