

Plastic tubing

PUN-H-1/4-BR-150-CB

Part number: 567996

FESTO

Approved for use in food processing (hydrolysis resistant)

This product is only available if ordered from the Festo Corporation, USA.



Data sheet

| Feature | Value |
|--|--|
| Outer diameter, inches | 1/4 |
| Bending radius relevant for flow rate | 0.085 Fuß |
| Min. bending radius | 0.032 Fuß |
| Temperature dependent working pressure | -14.4 ... 145 Psi |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Food safety | to manufacturer's declaration |
| Ambient temperature | -31 ... 145 °F |
| Product weight according to length | 0.23 oz/ft |
| Color | brown |
| Shore hardness | D 52 +/-3 |
| Materials note | Conforms to RoHS Free of copper and PTFE |
| Materials information for tubing | TPE-U(PU) |