

# Plastic tubing

## PUN-H-3/8-SI-500-HA

Part number: 568012

FESTO

Approved for use in food processing (hydrolysis resistant)

This product is only available if ordered from the Festo Corporation, USA.



### Data sheet

| Feature                                | Value  |
|--|--|
| Outer diameter, inches                 | 3/8  |
| Bending radius relevant for flow rate  | 0.171 Fuß  |
| Min. bending radius                    | 0.081 Fuß  |
| Temperature dependent working pressure | -14.4 ... 145 Psi  |
| Operating medium                       | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Food safety                            | to manufacturer's declaration                            |
| Ambient temperature                    | -31 ... 145 °F   |
| Product weight according to length     | 0.48 oz/ft   |
| Color                                  | silver   |
| Shore hardness                         | D 52 +/-3  |
| Materials note                         | Conforms to RoHS<br>Free of copper and PTFE              |
| Materials information for tubing       | TPE-U(PU)  |