

# Plastic tubing

## PEN-3/16-BL-150-CB

Part number: 569890

FESTO

standard O.D tubing, for QS plug connectors, polyethylene (not approved for use in the food industry).

This product is only available if ordered from the Festo Corporation, USA.



### Data sheet

Feature	Value
Outer diameter, inches	3/16
Bending radius relevant for flow rate	0.075 Fuß
Min. bending radius	0.039 Fuß
Temperature dependent working pressure	-14.4 ... 145 Psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Ambient temperature	-22 ... 140 °F
Product weight according to length	0.1 oz/ft
Color	blue
Shore hardness	D 52 +/-3
Materials note	Conforms to RoHS Free of copper and PTFE
Materials information for tubing	PE