

Plastic tubing PLN-1/2-SW-150-CB

Part number: 569910

FESTO

highly resistant to chemicals and hydrolysis.

This product is only available if ordered from the Festo Corporation, USA.



Data sheet

| Feature | Value |
|--|--|
| Outer diameter, inches | 1/2 |
| Bending radius relevant for flow rate | 0.213 Fuß |
| Min. bending radius | 0.138 Fuß |
| Temperature dependent working pressure | -14.4 ... 203 Psi |
| Certificate issuing department | TZW |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Food safety | to manufacturer's declaration |
| Ambient temperature | -22 ... 176 °F |
| Authorization | Drinking water KTW-A Drinking water W 270 |
| Product weight according to length | 0.58 oz/ft |
| Color | Black |
| Shore hardness | D 52 +/-3 |
| Materials note | Conforms to RoHS Free of copper and PTFE |
| Materials information for tubing | PE |