

Plastic tubing PAN-14X2-SI

Part number: 570392

FESTO



Data sheet

Feature	Value
Outside diameter	14 mm
Bending radius relevant for flow rate	80 mm
Inside diameter	10 mm
Min. bending radius	50 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.095 ... 1.7 MPa
Temperature dependent working pressure	-0.95 ... 17 bar
Temperature-dependent operating pressure	-13.775 ... 246.5 psi
Authorization	TÜV
Maritime classification	see certificate
Certificate issuing department	B 013277 0506 00
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:::]
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-30 ... 80 °C
Product weight according to length	0.077 kg/m
Pneumatic connection	For push-in connector outside diameter 14 mm
Color	silver
Shore hardness	D 55 +/-3
Materials note	Conforms to RoHS
Material tubing	TPE-A